

```

38 0E038      7CF202      _main      ENTER #02H
39          int cnt;
0E03B      F5DEFF      JSR.W _set_Mai 0E01AH
40          IO_port();
0E03E      F5CDFD      JSR.W _IO_port 0E00CH
41          pl_3=1;
0E041      7E9F1B07    BSET:G 3,00E9H
42          while(1)
0E045      D910      MOV.W:Q #1H,R0
0E047      6A2B      JEQ 0E079H
43          {
44          pl_3=0;
0E049      7E8F0B07    BCLR:G 3,00E1H
45          for(cnt=0; cnt<2000; cnt++): //wait 1msec
0E04D      D90BFE      MOV.W:Q #0H,-2H[FB]
0E050      778BFED007  CMP.W:G #07D0H,-2H[FB]
0E055      7DCA08      JGE 0E05DH
0E058      C91BFE      ADD.W:Q #1H,-2H[FB]
0E05B      FEF4      JMP.B 0E050H
46          pl_3=1;
0E05D      7E9F0B07    BSET:G 3,00E1H
47          for(cnt=0; cnt<2000; cnt++): //wait 1msec
0E061      D90BFE      MOV.W:Q #0H,-2H[FB]
0E064      778BFE204E  CMP.W:G #4E20H,-2H[FB]
0E069      7DCA08      JGE 0E071H
0E06C      C91BFE      ADD.W:Q #1H,-2H[FB]
0E06F      FEF4      JMP.B 0E064H
48          }
0E071      FED3      JMP.B 0E045H
49          }
50          }
51          EXITD

```

Range: -016009, 000000 Area: Break File: Cycle: -000023 Address: 00050B Time: 00'00'00:002.597

Cycle	Label	Address	Data	Size	Type	R/W	Interrupt	h' m' s: ms. us
-000023		00050B	07CE	DW	Data	W	-	-
-000022		00E05B	F4FE	DW	Code	R	-	00'00'00:002.597(
-000021		00E05C	F4	DB	Data	R	-	-
-000020		00E050	8B77	DW	Code	R	-	00'00'00:002.597(
-000019		00050B	07CE	DW	Data	R	-	-
-000018		00E055	CA7D	DW	Code	R	-	00'00'00:002.598(
-000017		00E058	1BC9	DW	Code	R	-	00'00'00:002.598(
-000016		00050B	07CE	DW	Data	R	-	-
-000015		00050B	07CF	DW	Data	W	-	-
-000014		00E05B	F4FE	DW	Code	R	-	00'00'00:002.598(

wait_test... nrcr0.a30

Range: -032767, 000000 Area: Break File: Cycle: -032767 Address: 00050B Time: 00'00'00:020.676

Cycle	Label	Address	Data	Size	Type	R/W	Interrupt	h' m' s: ms. us
-032767		00050B	3E21	DW	Data	W	-	-
-032766		00E05B	F4FE	DW	Code	R	-	00'00'00:020.676(
-032765		00E05C	F4	DB	Data	R	-	-
-032764		00E050	8B77	DW	Code	R	-	00'00'00:020.676(
-032763		00050B	3E21	DW	Data	R	-	-
-032762		00E055	CA7D	DW	Code	R	-	00'00'00:020.677(
-032761		00E058	1BC9	DW	Code	R	-	00'00'00:020.677(
-032760		00050B	3E21	DW	Data	R	-	-
-032759		00050B	3E22	DW	Data	W	-	-
-032758		00E05B	F4FE	DW	Code	R	-	00'00'00:020.677(
-032757		00E05C	F4	DB	Data	R	-	-
-032756		00E050	8B77	DW	Code	R	-	00'00'00:020.676(

